

Arm Sling

- Manufactured in Silva-Spacer with COOLMAX® and COOLMAX freshFX® EcoMade
- Helps to gain access to axilla area for hygiene purposes
- Will help support and aid lifting
- Reduces resident / care giver handling
- Can be used during a transfer or to provide support during a procedure
- Wash temp 95°C / 203°F
- Tumble dry on a low heat (max 50°C)

Product Codes and Specifications:



Silva-Spacer with
COOLMAX®
and COOLMAX
freshFX® EcoMade

A

B

One Size

B-ARM

35½" (90cm)

17¾" (45cm)

B-ARM

